

Typ	Výška v U	Rozměry v mm				Rozměry včetně obalu (mm)			Hmotnost včetně obalu (kg)	
		V *	Š	H	Užitná hloubka	H	W	D	Standard	Verze pro vysokou zátěž
ROF-15-60/60	15	788	600	600	590	960	640	640	50	-
ROF-18-60/60	18	921	600	600	590	1090	640	640	54	-
ROF-21-60/60	21	1055	600	600	590	1230	640	640	59	-
ROF-24-60/60	24	1188	600	600	590	1360	640	640	64	-
ROF-27-60/60	27	1321	600	600	590	1500	640	640	69	72
ROF-33-60/60	33	1588	600	600	590	1760	640	640	78	79
ROF-36-60/60	36	1721	600	600	590	1890	640	640	83	84
ROF-42-60/60	42	1988	600	600	590	2160	640	640	93	95
ROF-45-60/60	45	2121	600	600	590	2290	640	640	98	100
ROF-48-60/60	48	2255	600	600	590	2430	640	640	103	105
ROF-15-60/80	15	788	600	800	790	960	640	840	59	-
ROF-18-60/80	18	921	600	800	790	1090	640	840	64	-
ROF-21-60/80	21	1055	600	800	790	1230	640	840	69	-
ROF-24-60/80	24	1188	600	800	790	1360	640	840	74	-
ROF-27-60/80	27	1321	600	800	790	1500	640	840	80	85
ROF-33-60/80	33	1588	600	800	790	1760	640	840	91	96
ROF-36-60/80	36	1721	600	800	790	1890	640	840	98	99
ROF-42-60/80	42	1988	600	800	790	2160	640	840	107	109
ROF-45-60/80	45	2121	600	800	790	2290	640	840	114	116
ROF-48-60/80	48	2255	600	800	790	2430	640	840	118	120
ROF-15-60/100	15	788	600	1000	990	960	640	1040	72	-
ROF-18-60/100	18	921	600	1000	990	1090	640	1040	79	-
ROF-21-60/100	21	1055	600	1000	990	1230	640	1040	86	-
ROF-24-60/100	24	1188	600	1000	990	1360	640	1040	95	-
ROF-27-60/100	27	1321	600	1000	990	1500	640	1040	104	108
ROF-33-60/100	33	1588	600	1000	990	1760	640	1040	114	117
ROF-36-60/100	36	1721	600	1000	990	1890	640	1040	117	118
ROF-42-60/100	42	1988	600	1000	990	2160	640	1040	130	132
ROF-45-60/100	45	2121	600	1000	990	2290	640	1040	137	139
ROF-48-60/100	48	2255	600	1000	990	2430	640	1040	143	145
ROF-42-60/110	42	1988	600	1100	1090	2160	640	1210	137	-
ROF-42-60/120	42	1988	600	1200	1190	2160	640	1310	144	-
ROF-15-80/60	15	788	800	600	990	960	840	640	65	-
ROF-18-80/60	18	921	800	600	990	1090	840	640	70	-
ROF-21-80/60	21	1055	800	600	990	1230	840	640	75	-
ROF-24-80/60	24	1188	800	600	990	1360	840	640	80	-
ROF-27-80/60	27	1321	800	600	990	1500	840	640	86	101
ROF-33-80/60	33	1588	800	600	990	1760	840	640	98	116
ROF-36-80/60	36	1721	800	600	990	1890	840	640	107	130
ROF-42-80/60	42	1988	800	600	990	2160	840	640	115	139
ROF-45-80/60	45	2121	800	600	990	2290	840	640	123	149
ROF-48-80/60	48	2255	800	600	990	2430	840	640	131	158
ROF-15-80/80	15	788	800	800	790	960	840	840	70	-
ROF-18-80/80	18	921	800	800	790	1090	840	840	78	-
ROF-21-80/80	21	1055	800	800	790	1230	840	840	86	-
ROF-24-80/80	24	1188	800	800	790	1360	840	840	90	-
ROF-27-80/80	27	1321	800	800	790	1500	840	840	95	110
ROF-33-80/80	33	1588	800	800	790	1760	840	840	108	126
ROF-36-80/80	36	1721	800	800	790	1890	840	840	117	140
ROF-42-80/80	42	1988	800	800	790	2160	840	840	129	153
ROF-45-80/80	45	2121	800	800	790	2290	840	840	136	161
ROF-48-80/80	48	2255	800	800	790	2430	840	840	142	169
ROF-15-80/100	15	788	800	1000	990	960	840	1040	84	-
ROF-18-80/100	18	921	800	1000	990	1090	840	1040	90	-
ROF-21-80/100	21	1055	800	1000	990	1230	840	1040	96	-
ROF-24-80/100	24	1188	800	1000	990	1360	840	1040	102	-
ROF-27-80/100	27	1321	800	1000	990	1500	840	1040	119	134
ROF-33-80/100	33	1588	800	1000	990	1760	840	1040	136	154
ROF-36-80/100	36	1721	800	1000	990	1890	840	1040	144	166
ROF-42-80/100	42	1988	800	1000	990	2160	840	1040	152	176
ROF-45-80/100	45	2121	800	1000	990	2290	840	1040	160	186
ROF-48-80/100	48	2255	800	1000	990	2430	840	1040	168	195
ROF-42-80/110	42	1988	800	1100	1090	2160	840	1210	161	-
ROF-42-80/120	42	1988	800	1200	1190	2160	840	1310	170	-

* Výška v mm bez nožiček; výška s nožičkami + 16-45mm



CONTEG
to complete your network

© CONTEG, Na Vítězné pláni 1719/4, Praha 4 :: 2008-11-26

CONTEG nemůže přebírat žádnou odpovědnost za případné omyly nebo opomenutí.